

TECHNICAL SHEET

Name: Vertex Best Helmet

Code: 55240

Rope Access and Confined Space Kit - Petzl

Description

Helmet for works in suspension with polycarbonate shell, protects against electrical hazards and molten metal splashes, lateral deformation and use in low temperatures.
Head circumference: 53-63 cm.

The helmet features:

- Side slots for mounting hearing protection.
- Possible application of protective face shield.
- Slot for mounting PIXA headlamp.
- Four positioning hooks for mounting a headlamp with an elastic band.
- Chinstrap designed to decrease the risk of losing the helmet in case of a fall (breaking strength greater than 50 daN).

Weight: 455 g.

Features protection against Lateral Deformation LD and Molten Metal splash MM; 440V a.c. Electrical insulation; suitable for temperatures down to -30°C.

Vertex Best Helmet partially meets the requirements of EN 12492 EC and the standard EN 397 EC, in particular: the shell meets the requirements of electrical insulation EN 397, whereas the chinstrap meets the requirements of standards EN 12429; there being a contrast on the resistance of the chinstrap (between 15 and 25 N, according to EN 397, to avoid restriction and higher than 50 N according to EN 12492, to avoid the loss of the helmet in case of fall), the device cannot conform to any norm in particular, but only the CE marking, according to Directive 89/686/EEC, that sets the conditions for its placing on the market and the EU circulation, in addition to the basic safety requirements that the PPE must satisfy to grant the health and ensure the safety of the users.



Category

III

Colours

Yellow, White, Red, Orange, Black, Blue

Available Sizes

Unica

Quantity/Carton

1

Important Information

Read carefully the user sheet included.
Make sure the item is in good condition, undamaged before use. Once you become aware of a damage, you should immediately replace it.

Recommended for

The helmet shall be worn in combination with the other tree climbing work-positioning devices.

Dexterity

EC Standards

CE

Storage and cleaning

Keep in a cool dry place, far from heat sources.
Clean the shell with warm soapy water, then rinse with clear water. Do not use any solvents.